



PACKAGING TAPES

POLINAR

Traditional self-adhesive tape with natural rubber adhesive base in solvent, suited for use on hand dispensers and automatic sealing machines and for printing on flexographic machines with primer and release system.

The adhesion and elasticity characteristics, together with the brilliance and transparency, typical of Polypropylene films, make it ideal for all applications in the packaging sector.

Particularly suitable for use at low temperatures.

TECHNICAL SPECIFICATIONS

BACKING

Preprinted Polypropylene film

ADHESIVE

Natural rubber, hydrocarbonic and natural resins, pigments, plasticizers and antioxidants

POLINAR

POLINAR E

POLINAR EE

	POLINAR	POLINAR E	POLINAR EE	
Backing thickness	32 μ	28 μ	25 μ	± 10 %
Total thickness	50 μ	46 μ	43 μ	± 10 %
Adhesion	2,2 N/cm	2,2 N/cm	2,2 N/cm	± 10 %
Stretch at breaking point	145 %	145 %	145 %	± 20 %
Breaking load	50 N/cm	43 N/cm	40 N/cm	± 10 %
Colours	BROWN WHITE TRANSPARENT	BROWN WHITE TRANSPARENT	BROWN WHITE TRANSPARENT	

THE ABOVE VALUES ARE THE AVERAGE RESULTS OF TESTS MADE ON OUR STANDARD PRODUCTION AND ARE THEREFORE NOT LEGALLY BINDING.

COMPANY WITH QUALITY MANAGEMENT
SYSTEM CERTIFIED BY DNV
= ISO 9001:2008 =

NAR S.p.A. Via Leonardo da Vinci, 8 Z.I. - 35020 LEGNARO (PD) Italy

Telephone ++39 049 883 02 33 - Telefax ITA ++39 049 883 02 44 - Telefax EXP ++39 049 883 02 55

E-mail: narspa@nar-spa.com - www.nar-spa.com



STANDARD SIZES

ROLLS PER BOX

LENGTH IN METRES		WIDTH IN MM.	
66	x	9	192
66	x	12	144
66	x	15	120
66	x	19	96
66	x	25	72
66	x	30	60
66	x	38	48
66	x	48	36
66	x	50	36
66	x	75	24
132	x	38	48
132	x	50	36
990	x	50	6
990	x	75	4
990	x	100	3
990	x	150	2

OTHER SIZES AND PACKS ARE AVAILABLE ON REQUEST. PLEASE CONTACT OUR CUSTOMER SERVICE.

Polinar is also supplied printed, under the name POLINARPRINT and POLIPRINT E.



RECOMMENDATIONS FOR THE USE

- IT IS GOOD PRACTICE TO USE THE PRODUCT WITHIN 6 MONTHS FROM PURCHASE DATE. THE UNROLLING STRENGTH OF THE TAPE NORMALLY INCREASES IN TIME.
- THE TAPE MUST BE KEPT IN A DRY PLACE, PREFERABLY AT A TEMPERATURE BETWEEN 15°C AND 25°C. IF THE STORAGE TEMPERATURE IS DIFFERENT, BRING THE TAPE BACK TO ABOVE LEVEL BEFORE USING IT. KEEP IT OUT OF THE LIGHT.
- THE ROLLS MUST BE STORED HORIZONTALLY AND KEPT IN THEIR ORIGINAL PACKING.
- HANDLE THE PRODUCT WITH CARE TO AVOID DAMAGING IT AND CONSEQUENTLY, ALTERING ITS CORRECT USE.
- THE VALUES INDICATED IN THIS DATA SHEET REFER TO RESULTS OF TESTS MADE ON THE PRODUCT JUST MANUFACTURED. THE AESTHETIC AND TECHNICAL FEATURES OF THE TAPE MAY BE SUBJECT TO SOME CHANGES CONSEQUENT ON AGEING, EVEN THOUGH THE QUALITY LEVEL OF THE PRODUCT IS MAINTAINED.
- THIS PRODUCT HAS A WIDE RANGE OF APPLICATIONS. HOWEVER IT IS ADVISABLE TO CHECK THE USE IT IS MEANT FOR, THE SURFACE OF APPLICATION AND ITS CLEANLINESS.

NAR IS AT YOUR DISPOSAL FOR ANY FURTHER INFORMATION.

Under normal conditions the tape is not toxic and does not generally cause problems on contact with the skin. However, normal precautions should be taken in handling it and hands should be washed after use. The tape is not approved for medical use, for bandaging and contact with foodstuff.